



Pole Base Foundation, 10-3/4" OD x 120" Long

By CHANCE Foundation Solutions
Catalog # [T1121083](#)

Streetlight Foundation (SLF) 10.75 OD x 120" Long, 1" thick x 15-3/4" square baseplate, variable circle, hardware included.



*Representative Image

Features

- Variable 12" - 17" Bolt Circle
- 4 slots, 1-1/4" Dia x 4" Long
- hardware included
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

Application

Helical Anchoring

General

Coating	Galvanized
Number of Bolt Slots	4
Quantity of Hardware	4
Type	Lighting Foundation Anchors
UPC	096359709770
With Hardware	Included

Dimensions

Base Plate Dimensions	15.75 in
Base Plate Thickness	1.000 in
Bolt Length	4.00 in
Bolt Size	1 1/4 - 7 UNC x 4 in
Cableway Distance From Base	12 in
Cableway Length	12.00 in
Cableway Width	2.50 in
Center hole dimensions	7.00 in
Diameter - Bolt	1.25 in
Diameter - Bolt Circle	<ul style="list-style-type: none"> • 13.5 in • 16.5 in
Foundation Diameter	10.750 in
Foundation Length	120 in
Length	120.00 in
Length - Base Plate to Top of Conduit Hole	12 in
Pipe Wall Thickness	0.25
Weight	351.00 lb

Product Assets

- [Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
- [Engineering Drawing - SA1121083](#)
- [Installation Manuals - Instant Foundations \(TD04365E\)](#)
- [Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
- [Literature - Precast Concrete Collars \(SF04273E\)](#)
- [Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
- [Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
- [Sales Drawings - SA1121083_B](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
- [Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
- [Video - SLF \(VI04173E1021\)](#)
- [Video - CHANCE® Streetlight Foundation \(VI04147E0719\)](#)

Related Products

[C3030684](#)



