



2 Ton Hotstick Handle Nylon-Strap Ratchet Hoist

By Chance Lineman Tools & Equipment
Catalog # [PSC3090468](#)

Every Chain Hoist is proof-tested and factory-operated at 150% of capacity rating



*Representative Image

Features

- Always use with insulated link sticks of appropriate length
- Swivel-eye on handle end for operation via hot-line tools
- Hotstick rings on hooks and latches
- 2-Ton units employ a sheave-mounted hook in a double-strap bucket
- 3'9" Standard lift distance
- 27" minimum between hooks

General

EU RoHS Indicator	No
Strength Rating - Ultimate	4000 lb
Style	Hotstick Handle
UPC	096359470465
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

Dimensions

Dimensions	22 in x 8.38 in x 5 in
Height	5 in
Length	22 in
Length Metric	55.9 mm
Weight	20.9 lb
WeightMetric	7.8 kg
Width	8.38 in

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)
[Installation Manuals - Strap Hoist Instruction Manual \(TD09176E 2\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC3090468-SPEC-EN | REV 1/2024