

CSWEU2LED

DECORATIVE LED AC/EMERGENCY LIGHT

FEATURES

- LED Life-cycle exceeding 10 years
- Quick installation
- Dual-voltage 120 or 277VAC input
- Long-life Nickel Cadmium battery at 3.6VDC for UL recognized 90 minute emergency lighting
- Wet Location Listed for 10°C to 40°C(50°F-104°F)
- External Push-to-Test switch
- Wall or Ceiling Mount



SPECIFICATIONS

DESCRIPTION

- The CSWEU2LED is a wet location listed emergency lighting unit made of injection molded, high-impact, UV stabilized thermoplastic with a UL94 V-0 flammability rating
- The unit includes a clear poly-carbonate shield which is fully gasketed, the housing and enclosure have a white finish
- The LED lamp-heads are fully adjustable and glare-free
- The unit can be wall or ceiling mounted. The CSWEU2LED 12 LED's per lamp-head

driven at 1.15W at 3.6VDC. The front cover is secured by 2 stainless steel screws

- Housing includes a molded-in template for easy installation

APPLICATION

The CSWEU2LED can be applied in areas susceptible to rain and severe moisture, such as parking decks and outdoor commercial applications.

tradeSELECT®



RELATED PRODUCTS

- [Exit & Message Signs](#)
- [Emergency Lighting Units](#)
- [Battery Packs](#)
- [Remote Heads & Fixtures](#)

COMPLIANCES

- UL924 Listed for Wet Location
- NFPA 101
- NFPA 70
- OSHA

WARRANTY

- 2 year full unit warranty
- See [HLI Standard Warranty](#) for additional information


ORDERING GUIDE

Catalog Number	Description
CSWEU2LED	Clear poly-carbonate shield with White Thermoplastic Housing, Dual LED Lamps, UL Wet Location listed, 120/277VAC Input, 3.6VDC Output, 1.15W per lamp

INPUT POWER REQUIREMENTS

	120V	277V
CSWEU2LED	1.90 W	1.90 W

DIMENSIONS



Single Carton Weight	2.5 lbs.
Master Carton Quantity	6 each

Photometric files are available on the Compass website.