

Ball-Socket Ground Clamp for 30mm Ball, 5H

By Chance Lineman Tools & Equipment
Catalog # [PSC6003507](#)

5H Ball Stud Ground Clamp for 30mm Ball, tapped for threaded ferrule



Features

- Ball-stud ground clamp for 30mm ball-studs
- Tapped for 5/8"-11 UNC threaded ferrule
- Rated 47kA 15 cycles X/R=30
- Eye-screw for use with grip-all clamp-sticks

General

| | |
|-------------------------------------|--------------|
| Eye Screw/T-Handle | N/A |
| Installation Torque (in-lb) | |
| Ferrule Installation Torque (in-lb) | N/A |
| Thread Size | 5/8-11 UNC |
| UPC | 096359603047 |

Dimensions

| | |
|--------|---------|
| Weight | 1.36 lb |
|--------|---------|

Electrical Ratings

| | |
|-----------------|---------------|
| Amperage Rating | 47kA X/R = 30 |
|-----------------|---------------|

Certifications And Compliance

| | |
|----------------------------|------|
| Fault Current - ASTM Grade | 5H |
| Industry Standard(s) | ASTM |

Product Assets

[Catalogs - Grounding Equipment](#)