




Bus Bar Ground Clamp with Rated Stud, Type I-Class A-Grade 7H, 6.625" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # [PSCT6000844001](#)

Bus Bar Ground Clamp with Rated Stud, Type I-Class A-Grade 7H, 6.625" Jaw Opening



Features

- Bus-Bar Ground Clamp
- Continuous Current 400A
- Fault Current 68kA for 15 cycles X/R=30
- Main Line Range Max. 6-5/8" O.D. Bus
- Main Line Range Min. 3-1/2" O.D. Bus
- Rated 8.5" x 0.75" Stud
- ASTM Type I, Class A, Grade 7H
- Jaws Smooth
- Rated Stud

General

Eye Screw/T-Handle	300 in-lb
Installation Torque (in-lb)	
Material	Aluminum
UPC	096359599623

Dimensions

Weight	7.8 lb
--------	--------

Certifications and Compliance

Fault Current - ASTM Grade	7H
----------------------------	----

Logistics

Pallet Quantity	24
-----------------	----

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301_web\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSCT6000844001-SPEC-EN | REV 1/2024