



27 kV, 125 kV BIL, Type C Standard Polymer Cutout w/100A 12kAIC fuseholder

by CHANCE Utility
Catalog ID: CP710213P

27 kV, 125 kV BIL, Standard Type C Polymer Cutout with a 100A, 12kAIC fuseholder, parallel-groove connector and no bracket.

* Representative image

Product Details

General

| | |
|---------------------------------------|--------------|
| Bracket Type | No Bracket |
| Description - Replacement Fuse Holder | T710-213T |
| Type | Cutout |
| UPC | 096359380023 |

Dimensions

| | |
|--------|---------|
| Weight | 11.5 lb |
|--------|---------|

Electrical Ratings

| | |
|-----------------------------------|--|
| BIL | 125 kV |
| Creep and Leakage Distance | 17.1" (434mm) |
| Current Rating | 100 A |
| Fuselink Current Range | 1A to 100A - removable buttonhead fuse link only |
| Reference Voltage Limit - Minimum | Thru 24.9kV |
| Temperature Rise - Max. at 300A | 33° C |
| Voltage - Maximum | 27 kV |
| Voltage - Radio Interference | Ambient @15.66kV |
| Voltage Rating | 27 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 42 EA |
| Standard Package | 1 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com