




# 14.4 kV, 600 A, 110 kV BIL, Porcelain, Horizontal Three-Phase Loadbreak Switch

by CHANCE Utility  
Catalog ID: D7HE1CLD

14.4 kV, 110 kV LIW, 600A, Horizontal, Three-Phase Loadbreak Switch.



\* Representative image

## Product Details

### General

Blade Type	Tubular Copper (single-member)
Cantilever Bending Strength - Routine	2,000 Lbs (8.9 kN)
Color - Insulator	Sky Gray
Contact	Silver, Copper
Crossarm Brace Type	Fiberglass (4" x 4" Foam-Filled)
Insulator Type	Porcelain (3" Bolt Circle)
Material - Base	Galvanized Steel per ASTM A153
Material - Interphase Shaft	Fiberglass
Mounting Position	Horizontal
Tension Range	8000 lb
Torsional Strength	7,000 in Lbs (790.3 N-M)
UPC	096359035077

### Dimensions

Weight	696.78 lb
--------	-----------

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	15.5" (394mm)
Current - Under Loop Switching	600 A (4.8kV)
Current - Under Magnetizing Switching	7 A
Current Rating	600 A
Current Rating - Cable (Shielded)	100 A
Current Rating - Cable (Unshielded)	11 A
Dead-Ending Rating - Unequal Load	700Lbs
Dead-Ending Rating - Working Load	6000 Lbs
Depth - Ice Break	3/8"
Interrupt Rating - 600 A	50 Operations
Reference Voltage Limit - Minimum	14.4 kV
Temperature Rise - Max. at 600A	36°C

Voltage - Maximum	15.5 kV
Withstand Current - Short Time (10 cycles)	40kA, asymmetrical
Withstand Current - Short Time (3 sec)	25kA, symmetrical

### Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

### Logistics

Standard Package	1
------------------	---

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)