

**Overhead Switches CF-D 38kV**

By Delmar  
Catalog # [CF-D38400170SAH](#)

The single phase disconnect switch model CF-D is designed for switching lines overhead distribution systems. Provided of hooks for portable loadbreak tools. Manufactured and tested in accordance to ABNT / ANSI / IEC standards.

**Features**

- Hot dip galvanized steel base
- Porcelain and polymer support insulators
- High conductivity copper blade
- Self wiping, high pressure contacts with stainless steel spring
- Protective latch against unwanted opening
- Bronze alloy terminals with NEMA standard hole

**General**

Catalog Number                      CF-D38400170SAH

**Electrical Ratings**

BIL    170 kV



Creep and Leakage Distance	700 mm
Current Rating	400 A
Short Circuit Rating	42 kA
Voltage - Maximum	38 kV
Withstand Current - Short Time (1 sec)	16 kA
Withstand Voltage - Lightning Impulse (Phase to Ground)	80 kV
Withstand Voltage - Lightning Impulse (Terminal to Terminal)	88 kV

**Product Assets**

[Catalogs - Seccionadora de Distribuição CF-D 15kV a 38kV](#)  
[Specifications - CF-D38400170SAH](#)