



2.875" Round Shaft Lead (RS2875.276), 8/10/12/14 X 10ft High Capacity Pile

By CHANCE Foundation Solutions
Catalog # [C2788406](#)

RS2875.276, 120" long with 8",10",12",14" helices High Capacity Pile



Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

Application

Helical Anchoring

General

Capacity - Plate Grade	80 ksi
Coating	Galvanized
Finish Type	Galvanized
Helix Leading Edge Type	Sharp
Holding Capacity Soil (Kt)	9
Number of Helices	4
Shaft Type	RS
Torque Rating	10500 ft-lbs
Type	Lead Sections

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in - 14 in
Length	120.00 in
Length - Effective	120 in
Pipe Wall Thickness	0.276
Weight	127.50 lb

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Installation Manuals - Type RS2875.276 Helical Pile \(TD04341E\)](#)
[Installation Manuals - Type RS2875.276 Helical Pile Building Code \(TD04342E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Round Shaft Helical Piles \(BR04314E\)](#)
[Sales Drawings - Leads And Extensions Rs2875.276 High Capacity Pile](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - Chance Foundation Solutions Anchor/Pile Installation Tools \(VIO4146E0519\)](#)

Related Products

[C2788381 - 2.875" Round Shaft Extension \(RS2875.276\), 5ft High Capacity Pile](#)
[C2788382 - 2.875" Round Shaft Extension \(RS2875.276\), 7ft High Capacity Pile](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C2788406-SPEC-EN | REV 1/2024