



Wire-Ready Foundation, 3-1/2" OD x 64.5" Long

By CHANCE Foundation Solutions
Catalog # [T1120302](#)

Decorative Streetlight Foundation (SLF) , 3.5 OD x 64.5" Long, 3/4" thick x 12" square baseplate, variable circle, hardware included.



*Representative Image

Features

- Variable 5" - 12" Bolt Circle
- 4 slots, 5/8" Dia x 2-1/2" Long
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

Application

Helical Anchoring

General

Base Plate Shape	Square
Bolt Hole Type	Slotted
Coating	Galvanized
Ground Lug Hole	No
Hardware Packaging	Installed
Number of Bolt Slots	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359056089

Dimensions

Base Plate Dimensions	12.00 in
Base Plate Thickness	0.750 in
Bolt Length	2.50 in
Cableway Distance From Base	12 in
Cableway Length	1.25 in
Cableway Width	1.25 in
Center hole dimensions	3.60 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	• 5 in • 12 in
Foundation Diameter	3.500 in
Foundation Length	65 in
Weight	103.000 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- [Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
- [Engineering Drawing - SA1120302](#)
- [Installation Manuals - Instant Foundations \(TD04365E\)](#)
- [Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
- [Literature - Precast Concrete Collars \(SF04273E\)](#)
- [Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
- [Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
- [Sales Drawings - SA1120302](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
- [Video - CHANCE Instant Foundation & Concrete Collar \(VIO4163E0520\)](#)
- [Video - SLF \(VIO4173E1021\)](#)
- [Video - CHANCE® Streetlight Foundation \(VIO4147E0719\)](#)



A proud member of the Hubbell Family.

