

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

# ELOR Series

OUTDOOR LED REMOTE FOR ELSS CENTRAL BATTERY

## FEATURES

- Designed specifically for use with the ELSS Central Battery
- Provides outdoor LED path of egress illumination for up to 62' side to side spacing with 31' forward throw
- 3 High-Power LED's with adjustable lamp positioning
- White, Black and Dark Bronze finish



## RELATED PRODUCTS

- [ELSS Central Battery](#)
- [ELIR Indoor LED Remote](#)
- [ELWR Industrial Remote](#)



## SPECIFICATIONS

### APPLICATION

- Remotes do not include a battery which minimizes individual batteries throughout the space
- For use in new construction or retrofit
- For installation in commercial and architectural applications
- Mount from 7' to 20' high
- Small and compact size for architectural settings
- Eliminates battery maintenance in high mount applications

### CONSTRUCTION

- Housing and front cover constructed of die-cast aluminum, polycarbonate cover and LED lens
- Includes 1/2" conduit entry at top center of fixture
- Fully gasketed with Ball and Socket fasteners

### INSTALLATION

- Universal mounting template molded in the back of housing
- Input/output connection through surface conduit or wire entry from outlet box at rear of unit
- Unit mounts to all single gang and standard 3 1/2" and 4" square or octagonal electrical boxes

### OPERATING TEMPERATURE RANGE

- Wet Location Listed: -4° to 122°F (-20° to 50°C)

### COMPLIANCES

- Wet Location Listed to UL924 Standard
- Designed to NFPA101, NFPA70 requirements
- FCC Certified

### WARRANTY

- Full 5 year warranty
- See [HLI Standard Warranty](#) for additional information

## ORDERING GUIDE

Example: ELIR2

CATALOG #

Catalog Number	Description
ELORW	3 LED, 933 lumens, 8 watts, white finish
ELORB	3 LED, 933 lumens, 8 watts, black finish
ELORDB	3 LED, 933 lumens, 8 watts, dark bronze finish

KEY DATA	
Lamp Color	5000K
Total Lamp Output	
System Efficacy (LPW)	
Rated LED Lifecycle (Hours)	

DATE: \_\_\_\_\_ LOCATION: \_\_\_\_\_

TYPE: \_\_\_\_\_ PROJECT: \_\_\_\_\_

CATALOG #: \_\_\_\_\_

# ELOR Series

OUTDOOR LED REMOTE FOR ELSS CENTRAL BATTERY

Accessories	
ELSS	Central Battery
ELOR	Outdoor LED Remote
ELWR	Industrial NEMA 4X/IP66 Remote
EVE4X-DC ELSS	Thermoplastic Exit Sign
EVE4X-DC ELSS	DC NEMA 4X Exit Sign



ELSS Central Battery



ELIR Indoor Remote



ELWR NEMA 4X Remote



EVE-DC ELSS  
Thermoplastic Exit Sign



EVE4X-DC ELSS  
NEMA 4X/IP66 Exit Sign

## ELECTRONICS

The ELOR Outdoor LED remote includes a current sensitive LED driver module which regulates battery power at 800mA. An input and output connector provides input power to drive the LEDs. The input connection is not polarity sensitive. The output connector allows for multiple remotes to be connected in a daisy-chain. Remotes must be connected within 150' of the Central Battery which provides DC power when normal AC power is lost.

### LED Information

CCT: 5000K

CRI: XX



## REMOTE LOAD GUIDE



### ELOR Outdoor Remote

Part Number	Required Watts	Spacing (7.5MH)
ELOR	8W	31' Fwd x 62' Side

## DIMENSIONS



DATE: \_\_\_\_\_ LOCATION: \_\_\_\_\_

TYPE: \_\_\_\_\_ PROJECT: \_\_\_\_\_


CATALOG #: \_\_\_\_\_

# ELOR Series

OUTDOOR LED REMOTE FOR ELSS CENTRAL BATTERY

## APPLICATION INFORMATION

Single Unit Coverage



ELOR	Indoor	Outdoor
1 FC Average (Side X Forward)	62' x 31'	62' x 27'

**Mounting Height: 9'**  
**Side-To-Side: 6'**  
**Outdoor Reflectance: 0/30/10**  
**Indoor Reflectance: 80/50/20**

## PHOTOMETRY

### ELOR


#### LUMINAIRE DATA

Test No.	21.00113
Description	Outdoor Remote
Watts	8.3
Efficacy	90.5 lm/W
Mounting	Surface/Wall
Spacing Criterion	
0-DEG	3.93
90-DEG	1.86
180-DEG	0.54

#### ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	150	20.1
0-60	453	60.6
0-90	739	99
0-180	747	100

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

Angle	Candela (0.0)
0	91
5	91
15	109
25	143
35	184
45	269
55	1042
65	294
75	99
85	46
90	32