

CU2FO

FIXED OPTIC LED EMERGENCY LIGHT

tradeSELECT®

FEATURES

- LED life-cycle of more than 10 years
- Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- 12 LEDs per lamp-head for bright and even illumination
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- Provided with test switch and AC-On indicator
- Wall or Ceiling mount



RELATED PRODUCTS

Ø [CU2SO - Sealed Optic LED Emergency Light](#)

SPECIFICATIONS

DESCRIPTION

- The CU2FO offers quality and value with a compact and attractive LED based emergency light
- The white housing is made of high impact UL flame rated thermoplastic, and clear covers are made of impact resistant polycarbonate
- The fixed optic design provides consistent and predictable aiming
- Snap together design for quick and easy installation with option of wall or ceiling mount

APPLICATION

- The CU2FO can be applied in stairwells, hallways, offices and other commercial applications

- NFPA 70
- OSHA

COMPLIANCES

- UL924 Listed for Damp Location
- NFPA 101

WARRANTY


- 2 year full unit warranty
- See [HLI Standard Warranty](#) for additional information

ORDERING GUIDE

Catalog Number	Description	Accessories (Order Separately)
CU2FO	White Thermoplastic, Dual Head Emergency Light, 120/277 Input, Damp Location Listed, 3.6VDC, 1.74W per lamp-head, 144 lumens per head	WGEL 6.25"H x Wireguard 14"W x 4" D

ENERGY CONSUMPTION DIMENSIONS

	120 VAC	277 VAC
CU2FO	2.4W	2.3W



Single Carton Weight	2 lbs.
Master Carton Quantity	12 each