

CUSO

SLIM LED AC/EMERGENCY OUTDOOR LIGHT

FEATURES

- Includes self-diagnostic/self-test feature to monitor proper operation
- Quick installation
- Universal 120-277VAC input, 60Hz.
- Includes long-life 7.2V Nickel Cadmium battery for UL recognized 90 minute operation
- Full re-charge within 24 hours
- Provided with water-proof test switch and AC-On indicator
- 0°C to 50°C Standard Model, -25°C to 50°C with optional heater
- UL924 and Wet Location Listed



SPECIFICATIONS

DESCRIPTION

- The CUSO Series is an architectural, low-profile outdoor light, offering "normally On" AC and emergency lighting with powerful LED illumination
- The housing is fully sealed and gasketed, and has an IP65 rating
- Designed for wall mounting with universal K/O pattern in back-plate for easy installation to most standard size junction boxes
- Includes a single 1/2" NPT conduit entry in the top, center of the housing
- Illumination provided by 8 high power LEDs which achieve 1,600 lumens in AC and 600 lumens in emergency
- Available in 3000K or 4000K color temperature

- Models at 3000K include a photo-sensor and PIR(passive infra-red) motion detector which cannot be altered
- The unit will only turn on in AC mode when motion is detected. Models at 4000K include a photo-sensor and do not include motion detector
- The unit can be controlled by a switch, timer or the photo-cell

APPLICATION

- The CUSO Series can be applied in areas that are susceptible to rain and severe moisture like parking decks, and outdoor commercial applications to meet all Path of Egress requirements

ORDERING GUIDE

Catalog Number	Description
CUSO DB	Outdoor AC/EM, 3000K, Photo-sensor and PIR Motion Detect, Self-Diag., Dark Bronze
CUSO DB-H	Outdoor AC/EM, 3000K, Photo-sensor and PIR Motion Detect, Self-Diag., Dark Bronze, Heater
CUSO BK	Outdoor AC/EM, 3000K, Photo-sensor and PIR Motion Detect, Self-Diag., Black
CUSO BK-H	Outdoor AC/EM, 3000K, Photo-sensor and PIR Motion Detect, Self-Diag., Black, Heater
CUSO WH	Outdoor AC/EM, 3000K, Photo-sensor and PIR Motion Detect, Self-Diag., White
CUSO WH-H	Outdoor AC/EM, 3000K, Photo-sensor and PIR Motion Detect, Self-Diag., White, Heater
CUSO4DB-ND	Outdoor AC/EM, 4000K, Photo-sensor, Self-Diag., Dark Bronze
CUSO4DB-H-ND	Outdoor AC/EM, 4000K, Photo-sensor, Self-Diag., Dark Bronze, Heater
CUSO4BK-ND	Outdoor AC/EM, 4000K, Photo-sensor, Self-Diag., Black
CUSO4BK-H-ND	Outdoor AC/EM, 4000K, Photo-sensor, Self-Diag., Black, Heater
CUSO4WH-ND	Outdoor AC/EM, 4000K, Photo-sensor, Self-Diag., White
CUSO4WH-H-ND	Outdoor AC/EM, 4000K, Photo-sensor, Self-Diag., White, Heater

tradeSELECT®



RELATED PRODUCTS

- 🔗 [Exit & Message Signs](#)
- 🔗 [Emergency Lighting Units](#)
- 🔗 [Battery Packs](#)
- 🔗 [Remote Heads & Fixtures](#)

COMPLIANCES

- UL924 Listed for Wet Location
- NFPA 101
- NFPA 70
- OSHA



WARRANTY

- 5 year full unit warranty
- See [HLI Standard Warranty](#) for additional information

ENERGY CONSUMPTION

	Max.	Max. with heater
120VAC, 60Hz	3.59W	3.40W
277VAC, 60Hz	3.59W	3.40W

DIMENSIONS



Single Carton Weight	4 lbs.
Master Carton Quantity	6 each