

## SDC™ Composite Bushing - 5kV

By Electro Composites  
Catalog # 075-012-T-814-01

SDC™ 5kV-1200 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 1.0" Min. Oil Immersion Level/CT Pocket Length, 9.0" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

Transformer

### General

Bottom Terminal Type	1-14
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1-14
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	10.30 in
Below Flange Length	6.50 in
Diameter - Above Flange Maximum	5.21 in
Diameter - Below Flange Maximum D <gt;/> 1"	2.76 in
Diameter - Below Flange Maximum P	2.94 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	2.75 in
Effective Length - Bottom Terminal	1.75 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	5.25 in
Flange Mounting Hole Diameter	0.56 in
Flange Outside Diameter Length	6.25 in
Length - Ground Shield	1.00 in
Length - Insulation Above Flange	3.70 in
Length - Insulation Below Flange	2.40 in
Length - Live Part Bottom	3.10 in
Length - Live Part Top	3.30 in
Length - Minimum Oil Immersion Level	LOWER END TO BE FULLY IMMERSED
Sealing Surface Inside Diameter	3.01 in
Sealing Surface Outside Diameter	4.69 in
Top Terminal Min. Thread Length	2.50 in
Weight	15 lb

### Electrical Ratings

BIL	75 kV
Current Rating	1200 A
Minimum Creepage	9.00 in
Minimum Strike	4.80 in
Withstand Voltage - 60 Hz Dry	20 kV
kV Class	5 kV

## Certifications and Compliance

Industry Standard(s)

IEEE C57.19.01

### Product Assets

Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites  
Literature - Apparatus Bushings Selection Guide (TD02026E)  
Literature - SDC™ GSU Bushings - Electro Composites (SF02018E)  
Literature - SDC™ HV Generator Bushings - Electro Composites (SF02019E)  
Literature - SDC™ HV Bushings - Electro Composites (SF02017E)  
Literature - EC SDC Solid Dielectric Bushings v3  
Literature - FRENCH V2 - EC Generation Bushings  
Literature - FRENCH V2 - EC GSU Bushings  
Literature - How an SDC Bushing Test Tap is Constructed  
Sales Drawings - 814-01\_4958-10383



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-075-012-T-814-01-SPEC-EN | REV 1/2024