

CISCO AIR-ANT2566D4M-R PATCH ANTENNA ARTICULATING MOUNT



The AccelTex Solutions articulating mount for the Cisco AIR-ANT2566D4M-R allows installers to articulate the antenna horizontally and vertically to cover a specified area. This heavy duty mount is suitable for a wall, ceiling or pole installation and with the inscribed degree markings, provides maximum and precise articulation for the antenna.

Part Number: ATS-ANTMNT-HDART2566D

> MECHANICAL SPECIFICATIONS

Dimensions: 10" H x 10" W x 11.4" D (254mm H x 254mm W x 288.6mm D)

Weight: 3.15 lb (1.43 kg)
Installation: Wall/Pole Mount
Pole Mount Diameter: 2" (50mm)
Max Vertical Articulation ±85°
Max Horizontal Articulation: ±65°

> ENVIRONMENTAL SPECIFICATIONS

> WARRANTY

Installation Environment: Indoor or Outdoor

Wind Velocity: 130 mph (210 km/h)

1 Year Limited Warranty

> COMPATIBILITY

For use with the Cisco AIR-ANT2566D4M-R patch antenna.

> INCLUDED HARDWARE

Includes hardware to attach the Cisco antenna to the adapter plate, U-bolts for pole mounting and screws for wall mounting. Installer is required to provide any additional mounting/fastening hardware for other mounting situations (brick, concrete, etc.).