

By Pass Overhead Switches CF-B
38kV

By Delmar
Catalog # [CF-B38400630200](#)



The single phase Bypass switch model CF-B is designed to energize or de-energize reclosers and regulators in distribution systems without interruption of energy supply. Manufactured and tested in accordance to ABNT / ANSI / IEC standards

Features

- Hot dip galvanized steel base
- Porcelain support insulators
- High conductivity copper blade
- Self wiping, high pressure contacts with stainless steel spring
- Protective latch against unwanted opening
- Copper terminals with NEMA standard hole

General

Catalog Number CF-B38400630200

Electrical Ratings

BIL 200 kV
Creep and Leakage Distance 700 mm

Current Rating	400/630 A
Short Circuit Rating	65 kA
Voltage - Maximum	38 kV
Withstand Current - Short Time (1 sec)	25 kA
Withstand Voltage - Lightning Impulse (Phase to Ground)	70 kV
Withstand Voltage - Lightning Impulse (Terminal to Terminal)	77 kV

Product Assets

[Catalogs - Seccionadora By Pass CF-B 15kV a 38kV](#)
[Catalogs - Hookstick Operated Switches](#)
[Literature - HPS/CHANCE® TYPE BP3 SWITCH](#)
[Specifications - CF-B38400630200](#)