

SDC™ Composite Bushing - 8.7kV

By Electro Composites
Catalog # 095-040-T-478-00

SDC™ 8.7kV-4000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 17.75" Min. Oil Immersion Level/CT Pocket Length, 13.5" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	1X BLADE WITH 4X 0.69 DIA HOLES
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	4
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	4-10
Type	Condenser Bushings

Dimensions

Above Flange Length	13.38 in
Below Flange Length	25 in
Diameter - Above Flange Maximum	11.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	6.02 in
Diameter - Below Flange Maximum P	6.02 in
Diameter - Live Part Bottom	4.00 in
Diameter - Live Part Top	5.50 in
Effective Length - Bottom Terminal	4.25 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	10.88 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter Length	12.75 in
Length - Ground Shield	38.38 in
Length - Insulation Above Flange	17.75 in
Length - Insulation Below Flange	4.30 in
Length - Live Part Bottom	1.95 in
Length - Live Part Top	5.30 in
Length - Minimum Oil Immersion Level	4.70 in
Sealing Surface Inside Diameter	17.75 in
Sealing Surface Outside Diameter	6.24 in
Top Terminal Min. Thread Length	10.00 in
Weight	4.00 in
	192 lb

Electrical Ratings

BIL	95 kV
Current Rating	4000 A
Minimum Creepage	13.50 in
Minimum Strike	7.20 in
Withstand Voltage - 60 Hz Dry	38 kV
kV Class	8.7 kV

Certifications and Compliance

Industry Standard(s)

IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 478-00_5616-5386](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-095-040-T-478-00-SPEC-EN | REV 1/2024