

Distribution Arresters NLZ-P 27 kV

By Delmar
Catalog # [NLZP-2710](#)

The polymer distribution arresters model NLZ-P are designed to protect equipment against surges in distribution lines. Manufactured with metal oxide varistors without series gaps and UV resistant silicone rubber housing. Arresters are supplied with automatic ground lead disconnect. Assembled and tested in accordance to ABNT / ANSI / IEC standards.

Features

- Available in the rating of 3 kV to 36kV - 10kA
- Hot dip galvanized NEMA bracket
- Polymer insulating bracket
- Line and ground terminals for 10 to 2/0AWG cables
- High relief identification on the housing

General

Catalog Number	NLZP-2710
Residual Voltage (1 ? (max.))	96.40
Residual Voltage (8 x 20? (max.))	87.00

Dimensions



*Representative Image

Height	365 mm
Length	140 mm

Electrical Ratings

Creep and Leakage Distance	670 mm
Operating Voltage	22000 VAC
Voltage Rating	27 kV

Product Assets

- [Catalogs - Para-raios de Distribuição NLZ-P 3kV a 36kV](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
- [Specifications - NLZP-2710](#)