

Distribution Arresters NLZ-P 33 kV

By Delmar
Catalog # [NLZP-3310](#)

The polymer distribution arresters model NLZ-P are designed to protect equipment against surges in distribution lines. Manufactured with metal oxide varistors without series gaps and UV resistant silicone rubber housing. Arresters are supplied with automatic ground lead disconnect. Assembled and tested in accordance to ABNT / ANSI / IEC standards.

Features

- Available in the rating of 3 kV to 36kV - 10kA
- Hot dip galvanized NEMA bracket
- Polymer insulating bracket
- Line and ground terminals for 10 to 2/0AWG cables
- High relief identification on the housing

General

| | |
|-----------------------------------|-----------|
| Catalog Number | NLZP-3310 |
| Residual Voltage (1 ? (max.)) | 116.80 |
| Residual Voltage (8 x 20? (max.)) | 105.00 |

Dimensions



*Representative Image

| | |
|--------|--------|
| Height | 415 mm |
| Length | 140 mm |

Electrical Ratings

| | |
|----------------------------|-----------|
| Creep and Leakage Distance | 1000 mm |
| Operating Voltage | 26700 VAC |
| Voltage Rating | 33 kV |

Product Assets

- [Catalogs - Para-raios de Distribuição NLZ-P 3kV a 36kV](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
- [Specifications - NLZP-3310](#)