



Formed Wire Distribution Grip Deadend

by FARGO
Catalog ID: DGFW4549



* Representative image

Formed Wire Distribution Grip Deadend for ACSR (300 26/7-30/7, 336.4 18/1-36/1-26/7, 397.5 36/1), AAC (336.4 19W/37W, 350 19W/37W, 397.5 19W/37W, 400 19W/37W), AAAC (336.4 7W), Compacted ACSR (397.5 18/1) and AWAC® (336.4 18/1)

- For deadending bare or plastic jacketed conductor on primaries, secondaries, and substation feeder applications
- For use on ACSR, AAC, AAAC, Compacted ACSR and AWAC®
- Aluminum clad steel construction
- DGFW deadends will hold a minimum of 60% of the cable (RBS) rated breaking strength.

Product Details

General

Application	Deadend for Distribution Feeder
Color Code	Green
Material	Aluminum Clad Steel
Product Category	Overhead
Type	Formed Wire
UPC	096359451709

Dimensions

Length	38.6 in
Weight	2.108 lb

Conductor Related

Conductor Diameter - Maximum	0.739 in
Conductor Diameter - Minimum	0.654 in
Conductor Diameter Range	0.654 - 0.739
Conductor Type	ACSR, AAC, AAAC, Compacted ACSR and AWAC®

Logistics

Pallet Quantity	700 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com