

SDC™ Composite Bushing - 15kV

By Electro Composites
Catalog # 095-030-T-197-01

SDC™ 15kV-3000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 36.8" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEC 60137 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	3-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Tin
Top Terminal Type	3-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	28 in
Below Flange Length	21.5 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.03 in
Diameter - Below Flange Maximum P	5.03 in
Diameter - Live Part Bottom	3.00 in
Diameter - Live Part Top	4.50 in
Effective Length - Bottom Terminal	4.50 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	10.50 in
Length	49.50 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	18.20 in
Length - Insulation Below Flange	5.30 in
Length - Live Part Bottom	6.20 in
Length - Live Part Top	5.80 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	5.11 in
Sealing Surface Outside Diameter	8.62 in
Top Terminal Min. Thread Length	4.00 in
Weight	166 lb

Electrical Ratings

BIL	95 kV
Current Rating	3000 A
Minimum Creepage	36.80 in
Minimum Strike	20.70 in
Withstand Voltage - 60 Hz Dry	42 kV
kV Class	15 kV

Certifications and Compliance

Industry Standard(s)

IEC 60137

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 197-01_8818-8090](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-095-030-T-197-01-SPEC-EN | REV 1/2024