

SDC™ Composite Bushing - 15kV

By Electro Composites
Catalog # 110-030-T-797-00

SDC™ 15kV-3000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 27" Min. Oil Immersion Level/CT Pocket Length, 27.2" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	3-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Top Terminal	4
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1x Blade with 4x 0.56 Dia Holes
Type	Condenser Bushings

Dimensions

Above Flange Length	20 in
Below Flange Length	36 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.02 in
Diameter - Below Flange Maximum P	5.02 in
Diameter - Live Part Bottom	3.00 in
Diameter - Live Part Top	4.50 in
Effective Length - Bottom Terminal	4.75 in
Effective Length - Top Terminal	4.25 in
Flange Mounting Hole Bolt Circle	10.88 in
Flange Mounting Hole Diameter	0.56 in
Flange Outside Diameter Length	12.00 in
Length - Ground Shield	56.00 in
Length - Insulation Above Flange	27.00 in
Length - Insulation Below Flange	9.00 in
Length - Live Part Bottom	2.80 in
Length - Live Part Top	6.20 in
Length - Minimum Oil Immersion Level	7.10 in
Sealing Surface Inside Diameter	27.00 in
Sealing Surface Outside Diameter	5.13 in
Weight	9.88 in
	177 lb

Electrical Ratings

BIL	110 kV
Current Rating	3000 A
Minimum Creepage	27.20 in
Minimum Strike	11.90 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

Certifications and Compliance

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TDO2026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 797-00_8396-7810](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(VI00124E\)](#)



A proud member of the Hubbell Family.