

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 14.4kV

By Electro Composites  
 Catalog # [095-012-B-527-00](#)

SDC™ 14.4kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 18.5" Min. Oil Immersion Level/CT Pocket Length, 48.1" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

#### General

Application	OCB
Bottom Terminal Type	2.00 DIA SMOOTH WITH 1X GROOVE
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	No
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	24.38 in
Below Flange Length	30.63 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	3.13 in
Diameter - Below Flange Maximum P	3.13 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	3.00 in
Dimensions	55.00 in x 10.25 in x 10.25 in
Effective Length - Bottom Terminal	2.25 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	9 in
Flange Mounting Hole Diameter	0.56 in
Flange Outside Diameter	10.25 in
Height	10.25 in
Length	55 in
Length - Ground Shield	18.50 in
Length - Insulation Above Flange	15.90 in
Length - Insulation Below Flange	8.03 in
Length - Live Part Bottom	4.10 in
Length - Live Part Top	4.10 in
Length - Minimum Oil Immersion Level	18.50 in
Sealing Surface Inside Diameter	5.4 in
Sealing Surface Outside Diameter	7.48 in
Top Terminal Min. Thread Length	3 in
Weight	70 lb
Width	10.25 in

## Electrical Ratings

BIL	95 kV
Current Rating	1200 A
Minimum Creepage	48.1 in
Minimum Strike	18.4 in
Withstand Voltage - 60 Hz Dry	38 kV
kV Class	14.4 kV

## Certifications And Compliance

Industry Standard(s) IEC 60137

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 527-00\\_6064-5672](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-095012B52700-SPEC-EN | REV 6/2024