

HUBBELL

Power Systems

SDC™ Composite Bushing - 15kV

By Electro Composites
 Catalog # [095-012-T-461-00](#)

SDC™ 15kV-1200 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 22.2" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	15.12 in
Below Flange Length	16.88 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	2.98 in
Diameter - Below Flange Maximum P	2.98 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	32.00 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	2.38 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.75 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	32 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	6.70 in
Length - Insulation Below Flange	3.12 in
Length - Live Part Bottom	3.76 in
Length - Live Part Top	4.90 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	3.14 in
Sealing Surface Outside Diameter	6.5 in
Top Terminal Min. Thread Length	4 in
Weight	39 lb
Width	8.5 in

Electrical Ratings

BIL	95 kV
Current Rating	1200 A
Minimum Creepage	22.2 in
Minimum Strike	9.7 in
Withstand Voltage - 60 Hz Dry	38 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) IEC 60137

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 461-00_5451-5275](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-095012T46100-SPEC-EN | REV 6/2024