

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 15kV

By Electro Composites  
 Catalog # 110-004-T-434-05

SDC™ 15kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Drawlead Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 21" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Tin
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	16.19 in
Below Flange Length	14.63 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	2.73 in
Diameter - Below Flange Maximum P	2.73 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Dimensions	30.81 in x 8.50 in x 8.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.69 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	30.81 in
Length - Drawlead Above Flange	12.63 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	6.60 in
Length - Insulation Below Flange	3.53 in
Length - Live Part Bottom	1.10 in
Length - Live Part Top	5.40 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.56 in
Stud Inside Diameter	1 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	2.5 in
Weight	27 lb
Width	8.5 in

## Electrical Ratings

BIL	110 kV
Current Rating	400 A
Minimum Creepage	21 in
Minimum Strike	9 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

## Certifications And Compliance

Industry Standard(s)                      CSA C88.1

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 434-05\\_3547-8818](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-110004T43405-SPEC-EN | REV 6/2024