

HUBBELL

Power Systems

SDC™ Composite Bushing - 15kV

By Electro Composites
 Catalog # 110-004-T-448-01

SDC™ 15kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Drawlead Connected for Air-to-Oil Applications, 21.6" Min. Oil Immersion Level/CT Pocket Length, 19.4" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	17.06 in
Below Flange Length	26.25 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt/> 1"	3.12 in
Diameter - Below Flange Maximum P	3.24 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Dimensions	43.31 in x 8.50 in x 8.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	43.31 in
Length - Drawlead Above Flange	13.50 in
Length - Ground Shield	21.60 in
Length - Insulation Above Flange	6.60 in
Length - Insulation Below Flange	4.35 in
Length - Live Part Bottom	0.30 in
Length - Live Part Top	5.40 in
Length - Minimum Oil Immersion Level	21.60 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Stud Inside Diameter	1 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	2.5 in
Weight	37 lb
Width	8.5 in

Electrical Ratings

BIL	110 kV
Current Rating	400 A
Minimum Creepage	19.4 in
Minimum Strike	9 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) CSA C88.1

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 448-01_7632-7155](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-110004T44801-SPEC-EN | REV 6/2024