

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 15kV

By Electro Composites  
 Catalog # 110-012-T-706-00

SDC™ 15kV-1200 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 16.5" Min. Oil Immersion Level/CT Pocket Length, 19.2" Min. Creepage Length



#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	1 1/8-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/8-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	13.88 in
Below Flange Length	23 in
Diameter - Above Flange Maximum	5.21 in
Diameter - Below Flange Maximum D > 1"	2.76 in
Diameter - Below Flange Maximum P	2.94 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	2.75 in
Dimensions	36.88 in x 7.50 in x 7.50 in
Effective Length - Bottom Terminal	2.00 in
Effective Length - Top Terminal	2.00 in
Flange Mounting Hole Bolt Circle	6 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	7.5 in
Height	7.5 in
Length	36.88 in
Length - Ground Shield	16.50 in
Length - Insulation Above Flange	8.00 in
Length - Insulation Below Flange	3.30 in
Length - Live Part Bottom	3.20 in
Length - Live Part Top	2.80 in
Length - Minimum Oil Immersion Level	16.50 in
Sealing Surface Inside Diameter	3.01 in
Sealing Surface Outside Diameter	5.37 in
Top Terminal Min. Thread Length	2 in
Weight	31 lb
Width	7.5 in

## Electrical Ratings

BIL	110 kV
Current Rating	1200 A
Minimum Creepage	19.2 in
Minimum Strike	8.9 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

## Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 706-00\\_7520-7119](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-110012T70600-SPEC-EN | REV 6/2024