

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 15kV

By Electro Composites  
 Catalog # 110-012-W-774-00

SDC™ 15kV-1200 A Wall/Floor Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Air Applications, 5" Ground Shield/CT Pocket Length, 18.9" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

#### General

Application	Wall/Floor
Bottom Terminal Type	1 1/4-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Air
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	No
Top Terminal Plating	None
Top Terminal Type	1 1/4-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	14.06 in
Below Flange Length	15.94 in
Diameter - Above Flange Maximum	5.21 in
Diameter - Below Flange Maximum D <gt;/> 1"	2.76 in
Diameter - Below Flange Maximum P	2.95 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	2.75 in
Dimensions	30.00 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	7.5 in
Flange Mounting Hole Diameter	0.5 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	30 in
Length - Ground Shield	5.00 in
Length - Insulation Above Flange	7.80 in
Length - Insulation Below Flange	6.24 in
Length - Live Part Bottom	4.70 in
Length - Live Part Top	3.70 in
Length - Minimum Oil Immersion Level	NA
Sealing Surface Inside Diameter	3.01 in
Sealing Surface Outside Diameter	7 in
Top Terminal Min. Thread Length	3 in
Weight	153 lb
Width	8.5 in

## Electrical Ratings

BIL	110 kV
Current Rating	1200 A
Minimum Creepage	18.9 in
Minimum Creepage - Inside	6.60 in
Minimum Strike	8.9 in
Minimum Strike - Inside	6.00 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

## Certifications And Compliance

Industry Standard(s) CSA C88.1

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 774-00\\_8165-7613](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-110012W77400-SPEC-EN | REV 6/2024