

HUBBELL

Power Systems

SDC™ Composite Bushing - 15kV

By Electro Composites
 Catalog # 110-024-T-568-01

SDC™ 15kV-2400 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 30.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	20.1 in
Below Flange Length	20.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt/> 1"	3.48 in
Diameter - Below Flange Maximum P	3.48 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	3.50 in
Dimensions	40.60 in x 9.00 in x 9.00 in
Effective Length - Bottom Terminal	4.00 in
Effective Length - Top Terminal	3.50 in
Flange Mounting Hole Bolt Circle	7.5 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9 in
Height	9 in
Length	40.6 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	11.20 in
Length - Insulation Below Flange	5.80 in
Length - Live Part Bottom	4.70 in
Length - Live Part Top	4.30 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.62 in
Top Terminal Min. Thread Length	3.5 in
Weight	72 lb
Width	9 in

Electrical Ratings

BIL	110 kV
Current Rating	2400 A
Minimum Creepage	30.3 in
Minimum Strike	13.4 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 568-01_6633-6190](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-110024T56801-SPEC-EN | REV 6/2024