

HUBBELL

Power Systems

SDC™ Composite Bushing - 15KV

By Electro Composites
 Catalog # 110-033-T-921-00

SDC™ 15kV-3300A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21.0" Min.Oil Immersion Level/CT Pocket, 20.5" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	2 1/4-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	2 1/4-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	13.56 in
Below Flange Length	33.5 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D > 1"	4.15 in
Diameter - Below Flange Maximum P	4.17 in
Diameter - Live Part Bottom	2.50 in
Diameter - Live Part Top	4.00 in
Dimensions	47.06 in x 9.50 in x 9.50 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	2.38 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	9.5 in
Height	9.5 in
Length	47.06 in
Length - Drawlead Above Flange	NA
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	6.70 in
Length - Insulation Below Flange	30.20 in
Length - Live Part Bottom	3.30 in
Length - Live Part Top	3.30 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	7.62 in
Top Terminal Min. Thread Length	2.38 in
Weight	112 lb
Width	9.5 in

Electrical Ratings

BIL	110 kV
Current Rating	3300 A
Minimum Creepage	20.5 in
Minimum Creepage - Inside	NA
Minimum Strike	10 in
Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - SDC™ HV Bushings - Electro Composites](#)
[Sales Drawings - SDC Bushing 15kV, 3300A Model: 110-033-T-921-00](#)
[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand