

## SDC™ Composite Bushing - 15kV

By Electro Composites  
Catalog # 110-020-W-575-00

SDC™ 15kV-2000 A Wall/Floor Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Nitrogen Applications, 2" Ground Shield Length, 19.5" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

Wall/Floor

### General

Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Nitrogen
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	No
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	13.5 in
Below Flange Length	13.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.49 in
Diameter - Below Flange Maximum P	4.49 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Effective Length - Bottom Terminal	1.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.38 in
Flange Mounting Hole Diameter	0.50 in
Flange Outside Diameter Length	8.63 in
Length - Ground Shield	2.00 in
Length - Insulation Above Flange	6.60 in
Length - Insulation Below Flange	9.00 in
Length - Live Part Bottom	2.50 in
Length - Live Part Top	3.40 in
Length - Minimum Oil Immersion Level	NA
Sealing Surface Inside Diameter	5.11 in
Sealing Surface Outside Diameter	6.88 in
Top Terminal Min. Thread Length	2.50 in
Weight	38 lb

### Electrical Ratings

BIL	110 kV
Current Rating	2000 A
Minimum Creepage	19.50 in
Minimum Creepage - Inside	17.60 in
Minimum Strike	8.90 in
Withstand Voltage - 60 Hz Drv	50 kV

**Certifications and Compliance**

Industry Standard(s)

IEEE C57.19.01

**Product Assets**

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 575-00\\_6517-6100](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.