

HUBBELL

Power Systems

SDC™ Composite Bushing - 15 kV

By Electro Composites
 Catalog # 110-004-T-1043-01

SDC™ 15kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Drawlead Connected for Air-to-Oil Applications, 10.0" Min.Oil Immersion Level/CT Pocket, 20.8" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	15.4 in
Below Flange Length	13 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	4.00 in
Dimensions	28.415 in x 8.50 in x 8.50 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	28.415 in
Length - Drawlead Above Flange	11.85 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	6.70 in
Length - Insulation Below Flange	2.60 in
Length - Live Part Bottom	0.40 in
Length - Live Part Top	4.50 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Stud Inside Diameter	1.75 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	2.5 in
Weight	37 lb
Width	8.5 in

Electrical Ratings

BIL	110 kV
Current Rating	400 A
Minimum Creepage	20.8 in
Minimum Strike	9.9 in
Withstand Voltage - 60 Hz Dry	110 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) CSA C88.1

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 1043-01_7489-9908](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-110004T104301-SPEC-EN | REV 6/2024