

SDC™ Composite Bushing - 15KV

By Electro Composites
Catalog # 110-006-T-940-00

SDC™ 15kV-600DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Drawlead Connected for Air-to-Oil Applications, 1.5" Min.Oil Immersion Level/CT Pocket, 14.1" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

Application

Transformer

General

Bottom Terminal Type	None
Catalog Number	110-006-T-940-00
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	3
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/8-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	13.06 in
Below Flange Length	4.75 in
Diameter - Above Flange Maximum	5.75 in
Diameter - Below Flange Maximum D <gt; 1"	3.69 in
Diameter - Below Flange Maximum P	3.69 in
Diameter - Conductor Outside Under Insulation	1.25 in
Diameter - Live Part Bottom	1.25 in

Diameter - Live Part Top	3.50 in
Diameter - Rod / Tube	1.25/1.00 in
Dimensions	17.81 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	0.00 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	17.81 in
Length - Drawlead Above Flange	9.50 in
Length - Ground Shield	1.50 in
Length - Insulated Section	13 in
Length - Insulation Above Flange	5.50 in
Length - Insulation Below Flange	4.35 in
Length - Live Part Bottom	0.40 in
Length - Live Part Top	4.50 in
Length - Minimum Oil Immersion Level	LOWER END TO BE FULLY IMMERSED
Sealing Surface Inside Diameter	4.16 in
Sealing Surface Outside Diameter	6.62 in
Stud Inside Diameter	1 in
Thickness	1.22 in
Thread Size - Drawlead Connector	3/4-12
Top Terminal Min. Thread Length	2.5 in
Weight	19 lb
Width	8.5 in

Electrical Ratings

BIL	110 kV
Current Rating	600 A
Minimum Creepage	14.1 in
Minimum Creepage - Inside	NA
Minimum Strike	6.7 in
Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	50 kV

kV Class	15 kV	Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES DE TYPE GSU
Certifications And Compliance		Literature - SDC™ GSU Bushings - Electro Composites
Industry Standard(s)	IEEE C57.19.01	Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES POUR GÉNÉRATEUR
Product Assets		Literature - Apparatus Bushings Selection Guide
Catalogs - Electro Composites SDC™ composite bushings		Literature - ÉLECTRO COMPOSITES TRAVERSÉE HAUTE TENSION SDC™
Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites		Literature - SDC™ HV Bushings - Electro Composites
Literature - SDC™ HV Generator Bushings - Electro Composites		Sales Drawings - SDC Bushing 15kV, 600A Model: 110-006-T-940-00
Literature - How an SDC Bushing Test Tap is Constructed		Specifications - 110006T94000
		Video - ElectroComposites Factory Tour: St. Jerome



A Hubbell brand