

HUBBELL

Power Systems

SDC™ Composite Bushing - 15kV

By Electro Composites
 Catalog # 110-012-B-926-05

SDC™ 15kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 17" Min. Oil Immersion Level/CT Pocket Length, 21.1" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

General

Application	OCB
Bottom Terminal Type	2.36 Dia Smooth With 1x Groove
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	16.5 in
Below Flange Length	24.25 in
Diameter - Above Flange Maximum	5.21 in
Diameter - Below Flange Maximum D <gt;/> 1"	2.76 in
Diameter - Below Flange Maximum P	2.76 in
Diameter - Live Part Bottom	2.36 in
Diameter - Live Part Top	3.00 in
Dimensions	40.75 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	40.75 in
Length - Ground Shield	17.00 in
Length - Insulation Above Flange	9.80 in
Length - Insulation Below Flange	3.35 in
Length - Live Part Bottom	3.90 in
Length - Live Part Top	3.20 in
Length - Minimum Oil Immersion Level	17.00 in
Sealing Surface Inside Diameter	3.01 in
Sealing Surface Outside Diameter	6.37 in
Top Terminal Min. Thread Length	2.5 in
Weight	42 lb
Width	8.5 in

Electrical Ratings

BIL	110 kV
Current Rating	1200 A
Minimum Creepage	21.1 in
Minimum Strike	10.8 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) CSA C88.1

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 926-05_6640-10067](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-110012B92605-SPEC-EN | REV 6/2024