

SDC™ Composite Bushing - 26.4kV

By Electro Composites
Catalog # 150-004-T-589-00

SDC™ 26.4kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Drawlead Connected for Air-to-Oil Applications, 17" Min. Oil Immersion Level/CT Pocket Length, 30.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEC 60137 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Tin
Top Terminal Type	1 1/2-12
Type	Condenser Bushings

Dimensions

Above Flange Length	21.38 in
Below Flange Length	22.88 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.75 in
Flange Outside Diameter	8.50 in
Length	44.25 in
Length - Drawlead Above Flange	16.50 in
Length - Ground Shield	17.00 in
Length - Insulation Above Flange	11.20 in
Length - Insulation Below Flange	4.78 in
Length - Live Part Bottom	1.10 in
Length - Live Part Top	6.20 in
Length - Minimum Oil Immersion Level	17.00 in
Sealing Surface Inside Diameter	5.48 in
Sealing Surface Outside Diameter	5.88 in
Stud Inside Diameter	1.00 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	4.00 in
Weight	48 lb

Electrical Ratings

BIL	150 kV
Current Rating	400 A
Minimum Creepage	30.30 in
Minimum Strike	13.40 in

Withstand Voltage - 60 Hz 55 kV
Dry
kV Class 26.4 kV

Certifications and Compliance

Industry Standard(s) IEC 60137

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 589-00_6479-6211](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(VIO0124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-150-004-T-589-00-SPEC-EN | REV 1/2024