

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 15KV

By Electro Composites  
 Catalog # [110-012-T-890-00](#)

SDC™ 15kV-1200A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 8.5" Min.Oil Immersion Level/CT Pocket, 18.7" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	1X Blade With 2X 0.56 Dia Holes
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	2
Number of Bolt Holes - Top Terminal	4
Number of Flange Mounting Holes	3
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1X Blade With 4X 0.56 Dia Holes
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	17.47 in
Below Flange Length	17.63 in
Diameter - Above Flange Maximum	5.21 in
Diameter - Below Flange Maximum D > 1"	2.76 in
Diameter - Below Flange Maximum P	2.98 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	4.00 in
Dimensions	35.10 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	4.00 in
Effective Length - Top Terminal	4.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	35.1 in
Length - Drawlead Above Flange	NA
Length - Ground Shield	8.50 in
Length - Insulation Above Flange	7.70 in
Length - Insulation Below Flange	11.35 in
Length - Live Part Bottom	6.28 in
Length - Live Part Top	6.50 in
Length - Minimum Oil Immersion Level	8.50 in
Sealing Surface Inside Diameter	3.14 in
Sealing Surface Outside Diameter	6.62 in
Top Terminal Min. Thread Length	4 in
Weight	34 lb
Width	8.5 in

## Electrical Ratings

BIL	110 kV
Current Rating	1200 A
Minimum Creepage	18.7 in
Minimum Creepage - Inside	NA
Minimum Strike	8.7 in
Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

## Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - SDC™ HV Bushings - Electro Composites](#)  
[Sales Drawings - SDC Bushing 15kV, 1200A Model: 110-012-T-890-00](#)  
[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand