

HUBBELL Power Systems

SDC™ Composite Bushing - 15kV

By Electro Composites
Catalog # [110-020-T-355-02](#)

SDC™ 15kV-2000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 1.0" Ground Shield Length, 14.1" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	CONTACT DISC 3.00 DIA WITH 4X 1/2-13 THREADED HOLES ON 2.25 BC
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	4
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	No
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	11.4 in
Below Flange Length	5.2 in
Diameter - Above Flange Maximum	7.47 in
Diameter - Below Flange Maximum D <gt;/> 1"	2.98 in
Diameter - Below Flange Maximum P	2.98 in
Diameter - Live Part Bottom	3.00 in
Diameter - Live Part Top	3.25 in
Dimensions	16.60 in x 8.50 in x 8.50 in
Effective Length - Top Terminal	2.63 in
Flange Mounting Hole Bolt Circle	7.06 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	16.6 in
Length - Ground Shield	1.00 in
Length - Insulation Above Flange	4.20 in
Length - Insulation Below Flange	2.90 in
Length - Live Part Bottom	1.30 in
Length - Live Part Top	3.30 in
Length - Minimum Oil Immersion Level	LOWER END TO BE FULLY IMMERSED
Sealing Surface Inside Diameter	3.14 in
Sealing Surface Outside Diameter	6.43 in
Top Terminal Min. Thread Length	2.63 in
Weight	26 lb
Width	8.5 in

Electrical Ratings

BIL	110 kV
Current Rating	2000 A
Minimum Creepage	14.1 in
Minimum Strike	6.9 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	15 kV

Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Sales Drawings - 355-02_1756-10160](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-110020T35502-SPEC-EN | REV 6/2024