

## SDC™ Composite Bushing - 25kV

By Electro Composites  
Catalog # 150-050-T-728-00

SDC™ 25kV-5000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 48.2" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

Transformer

### General

Bottom Terminal Type	1x Blade with 6x 0.56 Dia Holes
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	6
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	4-12
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	23.75 in
Below Flange Length	33 in
Diameter - Above Flange Maximum	11.13 in
Diameter - Below Flange Maximum D <gt;/> 1"	6.02 in
Diameter - Below Flange Maximum P	6.21 in
Diameter - Live Part Bottom	4.00 in
Diameter - Live Part Top	5.50 in
Dimensions	56.75 in x 12.00 in x 12.00 in
Effective Length - Bottom Terminal	3.25 in
Effective Length - Top Terminal	3.50 in
Flange Mounting Hole Bolt Circle	10.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	12.00 in
Height	12.00 in
Length	56.75 in
Length - Ground Shield	21.00 in
Length - Insulation Above Flange	15.90 in
Length - Insulation Below Flange	7.60 in
Length - Live Part Bottom	4.40 in
Length - Live Part Top	4.60 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	6.24 in
Sealing Surface Outside Diameter	9.37 in
Top Terminal Min. Thread Length	3.50 in
Weight	298 lb
Width	12.00 in

### Electrical Ratings

BIL	150 kV
Current Rating	5000 A
Minimum Creepage	48.20 in
Minimum Strike	18.60 in

Minimum Strike	18.00 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

## Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Catalogs - Electro Composites SDC Bushings](#)  
[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 728-00\\_0002-7249](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-150-050-T-728-00-SPEC-EN | REV 1/2024