

## SDC™ Composite Bushing - 25kV

By Electro Composites  
Catalog # 150-070-G-767-00

SDC™ 25kV-7000 A GSU Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 10" Min. Oil Immersion Level/CT Pocket Length, 33.7" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

GSU

### General

Bottom Terminal Type	7-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	8
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	7-12
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	25.35 in
Below Flange Length	20.25 in
Diameter - Above Flange Maximum	13.00 in
Diameter - Below Flange Maximum D <gt;/> 1"	8.38 in
Diameter - Below Flange Maximum P	8.38 in
Diameter - Live Part Bottom	8.38 in
Diameter - Live Part Top	9.00 in
Effective Length - Bottom Terminal	5.17 in
Effective Length - Top Terminal	7.25 in
Flange Mounting Hole Bolt Circle	15.00 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	16.00 in
Length	45.60 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	12.60 in
Length - Insulation Below Flange	3.55 in
Length - Live Part Bottom	6.70 in
Length - Live Part Top	8.90 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Inside Diameter	9.87 in
Sealing Surface Outside Diameter	14.37 in
Top Terminal Min. Thread Length	7.25 in
Weight	399 lb

### Electrical Ratings

BIL	150 kV
Current Rating	7000 A
Minimum Creepage	33.70 in
Minimum Strike	14.80 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

## Certifications and Compliance

Industry Standard(s)

IEEE C57.19.01

### Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)  
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)  
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)  
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)  
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)  
[Literature - EC SDC Solid Dielectric Bushings v3](#)  
[Literature - FRENCH V2 - EC Generation Bushings](#)  
[Literature - FRENCH V2 - EC GSU Bushings](#)  
[Literature - How an SDC Bushing Test Tap is Constructed](#)  
[Sales Drawings - 767-00\\_8121-7569](#)  
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-150-070-G-767-00-SPEC-EN | REV 1/2024