

HUBBELL

Power Systems

SDC™ Composite Bushing - 26.4kV

By Electro Composites
 Catalog # [150-004-T-589-00](#)

SDC™ 26.4kV-400DL A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Drawlead Connected for Air-to-Oil Applications, 17" Min. Oil Immersion Level/CT Pocket Length, 30.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	None
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Tin
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	21.9 in
Below Flange Length	22.88 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	1.25 in
Diameter - Live Part Top	3.50 in
Dimensions	44.78 in x 8.50 in x 8.50 in
Effective Length - Top Terminal	4.53 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.75 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	44.78 in
Length - Drawlead Above Flange	16.50 in
Length - Ground Shield	17.00 in
Length - Insulation Above Flange	11.20 in
Length - Insulation Below Flange	4.78 in
Length - Live Part Bottom	1.10 in
Length - Live Part Top	6.8 in
Length - Minimum Oil Immersion Level	17.00 in
Sealing Surface Inside Diameter	5.48 in
Sealing Surface Outside Diameter	5.88 in
Stud Inside Diameter	1 in
Thread Size - Drawlead Connector	3/4-10
Top Terminal Min. Thread Length	4.53 in
Weight	48 lb
Width	8.5 in

Electrical Ratings

BIL	150 kV
Current Rating	400 A
Minimum Creepage	30.3 in
Minimum Strike	13.4 in
Withstand Voltage - 60 Hz Dry	55 kV
kV Class	26.4 kV

Certifications And Compliance

Industry Standard(s) IEC 60137

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 589-00_6479-6211](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
EC-150004T58900-SPEC-EN | REV 6/2024