

HUBBELL

Power Systems

SDC™ Composite Bushing - 27.5KV

By Electro Composites
 Catalog # 150-012-T-896-00

SDC™ 27.5kV-1200A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 8.0" Min.Oil Immersion Level/CT Pocket, 26.6" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets CSA C88.1 Electrical and Mechanical Requirements

General

Application	Transformer
Bottom Terminal Type	1 1/8-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4X / 3X
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	15.77 in
Below Flange Length	15.63 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D > 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	3.38 in
Diameter - Live Part Top	3.00 in
Dimensions	31.40 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	3.38 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	31.4 in
Length - Drawlead Above Flange	NA
Length - Ground Shield	8.00 in
Length - Insulation Above Flange	9.00 in
Length - Insulation Below Flange	11.33 in
Length - Live Part Bottom	4.30 in
Length - Live Part Top	3.40 in
Length - Minimum Oil Immersion Level	8.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.5 in
Top Terminal Min. Thread Length	2.5 in
Weight	46 lb
Width	8.5 in

Electrical Ratings

BIL	150 kV
Current Rating	1200 A
Minimum Creepage	26.6 in
Minimum Creepage - Inside	NA
Minimum Strike	11.5 in
Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	70 kV
kV Class	27.5 kV

Certifications And Compliance

Industry Standard(s)	CSA C88.1
----------------------	-----------

Product Assets

- [Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
- [Literature - SDC™ HV Bushings - Electro Composites](#)
- [Sales Drawings - SDC Traversée 27.5kV, 1200A Modèle: 150-0120T-896-00](#)
- [Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand