

HUBBELL

Power Systems

SDC™ Composite Bushing - 28.4kV

By Electro Composites
 Catalog # [150-012-W-067-00](#)

SDC™ 28.4kV-1200 A Wall/Floor Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEC 60137, Bottom Connected for Air-to-Air Applications, 10" Ground Shield/CT Pocket Length, 26.4" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEC 60137 Electrical and Mechanical Requirements

General

Application	Wall/Floor
Bottom Terminal Type	CONTACT DISC 1.50 DIA WITH 2X M8X1.25 HOLES ON 0.78 DIA BC
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Air
Material - Flange	Epoxy
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	2
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	Silver
Test Tap	No
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	19 in
Below Flange Length	20.31 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.49 in
Diameter - Below Flange Maximum P	5.00 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	39.31 in x 8.64 in x 8.64 in
Effective Length - Top Terminal	3.95 in
Flange Mounting Hole Bolt Circle	6.5 in
Flange Mounting Hole Diameter	1/2-13
Flange Outside Diameter	8.64 in
Height	8.64 in
Length	39.31 in
Length - Ground Shield	10.00 in
Length - Insulation Above Flange	14.60 in
Length - Insulation Below Flange	10.06 in
Length - Live Part Bottom	0.25 in
Length - Live Part Top	4.40 in
Length - Minimum Oil	NA
Immersion Level	
Sealing Surface Inside Diameter	5 in
Sealing Surface Outside Diameter	7.55 in
Top Terminal Min. Thread Length	3.95 in
Weight	60 lb
Width	8.64 in

Electrical Ratings

BIL	150 kV
Current Rating	1200 A
Minimum Creepage	26.4 in
Minimum Creepage - Inside	28.00 in
Minimum Strike	16.52 in
Withstand Voltage - 60 Hz Dry	50 kV
kV Class	28.4 kV

Certifications And Compliance

Industry Standard(s)	IEC 60137
----------------------	-----------

Product Assets

- [Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
- [Sales Drawings - 067-00_1001-0849](#)
- [Video - ElectroComposites Factory Tour: St. Jerome](#)