

SDC™ Composite Bushing - 25kV

By Electro Composites
Catalog # 150-020-T-570-03

SDC™ 25kV-2000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 26.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

Bottom Terminal Type	2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	3
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	16.90 in
Below Flange Length	28.25 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.15 in
Diameter - Below Flange Maximum P	4.15 in
Diameter - Live Part Bottom	2.00 in
Diameter - Live Part Top	3.50 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.63 in
Flange Outside Diameter Length	8.50 in
Length - Ground Shield	45.13 in
Length - Insulation Above Flange	21.00 in
Length - Insulation Below Flange	8.90 in
Length - Live Part Bottom	3.65 in
Length - Live Part Top	3.60 in
Length - Minimum Oil Immersion Level	4.30 in
Sealing Surface Inside Diameter	21.00 in
Sealing Surface Outside Diameter	4.37 in
Top Terminal Min. Thread Length	6.62 in
Weight	3.00 in
	83 lb

Electrical Ratings

BIL	150 kV
Current Rating	2000 A
Minimum Creepage	26.30 in
Minimum Strike	11.30 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Sales Drawings - 570-03_3089-10107](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-150-020-T-570-03-SPEC-EN | REV 1/2024