

SDC™ Composite Bushing - 25 kV

By Electro Composites
Catalog # 150-030-T-1032-00

SDC™ 25kV-3000A Wall/Floor Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 27.0" Min.Oil Immersion Level/CT Pocket Length, 34.3" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

Transformer

General

| | |
|---------------------------------|---|
| Bottom Terminal Type | 3-12 |
| Color | Gray |
| Immersion Type - Above Flange | Air |
| Immersion Type - Below Flange | Oil |
| Material - Flange | Aluminum |
| Material - Insulation | APG-15NA - High Temp Cycloaliphatic Epoxy |
| Mounting Position | Vertical to Horizontal |
| Number of Flange Mounting Holes | 6 |
| Plating - Bottom Terminal | None |
| Test Tap | Yes |
| Top Terminal Plating | None |
| Top Terminal Type | 1x Blade with 4X 0.56 DIA HOLES |
| Type | Condenser Bushings |

Dimensions

| | |
|---|----------|
| Above Flange Length | 22.3 in |
| Below Flange Length | 38 in |
| Diameter - Above Flange Maximum | 10.13 in |
| Diameter - Below Flange Maximum D <gt;/> 1" | 5.02 in |
| Diameter - Below Flange Maximum P | 5.02 in |
| Diameter - Live Part Bottom | 3.00 in |
| Diameter - Live Part Top | 4.50 in |
| Effective Length - Bottom Terminal | 4.75 in |
| Effective Length - Top Terminal | 4.25 in |
| Flange Mounting Hole Bolt Circle | 10.88 in |
| Flange Mounting Hole Diameter | 0.56 in |
| Flange Outside Diameter Length | 12.00 in |
| Length - Ground Shield | 60.25 in |
| Length - Insulation Above Flange | 27.00 in |
| Length - Insulation Below Flange | 11.3 in |
| Length - Live Part Bottom | 4.4 in |
| Length - Live Part Top | 6.6 in |
| Length - Minimum Oil Immersion Level | 7.0 in |
| Sealing Surface Inside Diameter | 27.0 in |
| Sealing Surface Outside Diameter | 5.11 in |
| Thread Size - Drawlead Connector | 9.88 in |
| Weight | NA |
| | 194 lb |

Electrical Ratings

| | |
|-------------------------------|---------|
| BIL | 150 kV |
| Current Rating | 3000 A |
| Minimum Creepage | 34.3 in |
| Minimum Strike | 14.0 in |
| Withstand Voltage - 60 Hz Dry | 60 kV |
| kV Class | 25 kV |

Certifications and Compliance

Industry Standard(s)

IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - 1032-00_1195-9752](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(VI00124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-150-030-T-1032-00-SPEC-EN | REV 1/2024