

SDC™ Composite Bushing - 25kV

By Electro Composites
Catalog # 150-060-G-507-01

SDC™ 25kV-6000 A GSU Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 16" Min. Oil Immersion Level/CT Pocket Length, 38.5" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

GSU

General

Bottom Terminal Type	6-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	8
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	6.00 DIA SMOOTH WITH 2X GROOVES
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	27.57 in
Below Flange Length	29.63 in
Diameter - Above Flange Maximum	13.00 in
Diameter - Below Flange Maximum D <gt;/> 1"	8.38 in
Diameter - Below Flange Maximum P	8.38 in
Diameter - Live Part Bottom	8.38 in
Diameter - Live Part Top	8.88 in
Effective Length - Bottom Terminal	4.50 in
Effective Length - Top Terminal	6.20 in
Flange Mounting Hole Bolt Circle	14.00 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter Length	16.00 in
Length - Ground Shield	57.20 in
Length - Insulation Above Flange	16.00 in
Length - Insulation Below Flange	14.10 in
Length - Live Part Bottom	7.83 in
Length - Live Part Top	5.80 in
Length - Minimum Oil Immersion Level	7.13 in
Sealing Surface Inside Diameter	16.00 in
Sealing Surface Outside Diameter	8.88 in
Weight	11.13 in
	378 lb

Electrical Ratings

BIL	150 kV
Current Rating	6000 A
Minimum Creepage	38.50 in
Minimum Strike	16.80 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

Certifications and Compliance

Product Assets

Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites
Literature - Apparatus Bushings Selection Guide (TDO2026E)
Literature - SDC™ GSU Bushings - Electro Composites (SF02018E)
Literature - SDC™ HV Generator Bushings - Electro Composites (SF02019E)
Literature - SDC™ HV Bushings - Electro Composites (SF02017E)
Literature - EC SDC Solid Dielectric Bushings v3
Literature - FRENCH V2 - EC Generation Bushings
Literature - FRENCH V2 - EC GSU Bushings
Literature - How an SDC Bushing Test Tap is Constructed
Sales Drawings - 507-01_6609-6357
Video - ElectroComposites Factory Tour: St. Jerome (VI00124E)



A proud member of the Hubbell Family.