

SDC™ Composite Bushing - 25KV

By Electro Composites
Catalog # 150-060-G-941-00

SDC™ 25kV-6000A GSU Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 11.0" Min.Oil Immersion Level/CT Pocket, 36.9" Min. Creepage Length



*Representative Image

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

Application

GSU

General

Bottom Terminal Type	1X Blade With 4X 0.69 Dia Holes
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	4
Number of Bolt Holes - Top Terminal	24
Number of Flange Mounting Holes	6
Plating - Bottom Terminal	Silver
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	4X Blades With 6X 0.69 Dia Holes
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	23 in
Below Flange Length	23.50 in
Diameter - Above Flange Maximum	13.00 in
Diameter - Below Flange Maximum D <gt;/> 1"	8.38 in
Diameter - Below Flange Maximum P	8.38 in
Diameter - Live Part Bottom	8.38 in
Diameter - Live Part Top	10.00 in
Effective Length - Bottom Terminal	4.20 in
Effective Length - Top Terminal	3.88 in
Flange Mounting Hole Bolt Circle	12.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	14.00 in
Length	46.50 in
Length - Drawlead Above Flange	NA
Length - Ground Shield	11.00 in
Length - Insulation Above Flange	14.10 in
Length - Insulation Below Flange	17.60 in
Length - Live Part Bottom	5.90 in
Length - Live Part Top	4.80 in
Length - Minimum Oil Immersion Level	11.00 in
Sealing Surface Inside Diameter	9.87 in
Sealing Surface Outside Diameter	11.37 in
Top Terminal Min. Thread Length	3.88 in
Weight	290 lb

Electrical Ratings

BIL	150 kV
Current Rating	6000 A
Minimum Creepage	36.9 in
Minimum Creepage - Inside	NA
Minimum Strike	15.1 in

Minimum Strike - Inside	NA
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

Certifications and Compliance

Industry Standard(s) IEEE C57.19.01

Product Assets

[Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites](#)
[Literature - Apparatus Bushings Selection Guide \(TD02026E\)](#)
[Literature - SDC™ GSU Bushings - Electro Composites \(SF02018E\)](#)
[Literature - SDC™ HV Generator Bushings - Electro Composites \(SF02019E\)](#)
[Literature - SDC™ HV Bushings - Electro Composites \(SF02017E\)](#)
[Literature - EC SDC Solid Dielectric Bushings v3](#)
[Literature - FRENCH V2 - EC Generation Bushings](#)
[Literature - FRENCH V2 - EC GSU Bushings](#)
[Literature - How an SDC Bushing Test Tap is Constructed](#)
[Sales Drawings - SDC GSU Bushing 25kV, 6000A Model: 150-060-G-941-00 \(S-1867-3036\)](#)
[Video - ElectroComposites Factory Tour: St. Jerome \(V100124E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
EC-150-060-G-941-00-SPEC-EN | REV 1/2024