

## SDC™ Composite Bushing - 25kV

By Electro Composites  
Catalog # 150-140-G-1016-00

SDC™ 25kV-14000 A GSU Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 18.5" Min. Oil Immersion Level/CT Pocket Length, 22.7" Min. Creepage Length



\*Representative Image

### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-15NA High Temperature Cycloaliphatic Epoxy Compound for high temperature applications
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements
- Can be mounted vertically or horizontally

### Application

GSU

### General

Bottom Terminal Type	CONTACT DISC 9.88 DIA WITH 12x 3/4-10 Holes on 7.50 BC
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-15NA - High Temp Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Bolt Holes - Bottom Terminal	12
Number of Bolt Holes - Top Terminal	40
Number of Flange Mounting Holes	12
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	Silver
Top Terminal Type	4x Blades with 10x 0.69 Dia Holes
Type	SDC - Solid Dielectric Capacitor

### Dimensions

Above Flange Length	18.16 in
Below Flange Length	25.56 in
Diameter - Above Flange Maximum	15.75 in
Diameter - Below Flange Maximum D <gt;/> 1"	12.50 in
Diameter - Below Flange Maximum P	12.50 in
Diameter - Live Part Bottom	12.50 in
Diameter - Live Part Top	13.81 in
Effective Length - Top Terminal	3.88 in
Flange Mounting Hole Bolt Circle	18.50 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	20.00 in
Length	43.73 in
Length - Ground Shield	18.50 in
Length - Insulation Above Flange	9.90 in
Length - Insulation Below Flange	4.86 in
Length - Live Part Bottom	2.20 in
Length - Live Part Top	4.80 in
Length - Minimum Oil Immersion Level	18.50 in
Sealing Surface Inside Diameter	13.18 in
Sealing Surface Outside Diameter	17.62 in
Weight	423 lb

### Electrical Ratings

BIL	150 kV
Current Rating	14000 A
Minimum Creepage	22.70 in
Minimum Strike	10.50 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

### Certifications and Compliance

Industry Standard(s)	IEEE C57.19.01
----------------------	----------------

## Product Assets

Installation Manuals - SDC™ Bushing General Handling and Maintenance Guide - Electro Composites  
Literature - Apparatus Bushings Selection Guide (TD02026E)  
Literature - SDC™ GSU Bushings - Electro Composites (SF02018E)  
Literature - SDC™ HV Generator Bushings - Electro Composites (SF02019E)  
Literature - SDC™ HV Bushings - Electro Composites (SF02017E)  
Literature - EC SDC Solid Dielectric Bushings v3  
Literature - FRENCH V2 - EC Generation Bushings  
Literature - FRENCH V2 - EC GSU Bushings  
Literature - How an SDC Bushing Test Tap is Constructed  
Sales Drawings - 1016-00\_1769-9584  
Video - ElectroComposites Factory Tour: St. Jerome (V100124E)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
EC-150-140-G-1016-00-SPEC-EN | REV 1/2024