

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 25 kV

By Electro Composites  
 Catalog # [150-030-T-1026-00](#)

SDC™ 25kV- 3000A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 14.8" Min.Oil Immersion Level/CT Pocket, 34.8" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

#### General

Application	Transformer
Bottom Terminal Type	1 1/2-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	20.5 in
Below Flange Length	23 in
Diameter - Above Flange Maximum	10.13 in
Diameter - Below Flange Maximum D > 1"	3.74 in
Diameter - Below Flange Maximum P	3.74 in
Diameter - Live Part Bottom	2.50 in
Diameter - Live Part Top	4.00 in
Dimensions	43.50 in x 8.50 in x 8.50 in
Effective Length - Bottom Terminal	2.50 in
Effective Length - Top Terminal	3.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Height	8.5 in
Length	43.5 in
Length - Ground Shield	14.8 in
Length - Insulation Above Flange	11.4 in
Length - Insulation Below Flange	4.1 in
Length - Live Part Bottom	4.1 in
Length - Live Part Top	5.2 in
Length - Minimum Oil Immersion Level	14.8 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Stud Inside Diameter	0.88 in
Top Terminal Min. Thread Length	3.5 in
Weight	100 lb
Width	8.5 in

## Electrical Ratings

BIL	150 kV
Current Rating	3000 A
Minimum Creepage	34.8 in
Minimum Strike	14.5 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

## Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 1026-00\\_1722-9706](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-150030T102600-SPEC-EN | REV 6/2024