

# HUBBELL

## Power Systems

### SDC™ Composite Bushing - 25kV

By Electro Composites  
 Catalog # 150-012-B-926-02

SDC™ 25kV-1200 A OCB Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 15.5" Min. Oil Immersion Level/CT Pocket Length, 21.1" Min. Creepage Length



\*Representative Image

#### Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

#### General

Application	OCB
Bottom Terminal Type	1 1/8-12
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	3
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	1 1/2-12
Type	SDC - Solid Dielectric Capacitor

#### Dimensions

Above Flange Length	16.5 in
Below Flange Length	24.38 in
Diameter - Above Flange Maximum	5.21 in
Diameter - Below Flange Maximum D <gt;/> 1"	2.76 in
Diameter - Below Flange Maximum P	2.76 in
Diameter - Live Part Bottom	1.50 in
Diameter - Live Part Top	3.00 in
Dimensions	40.88 in x 9.00 in x 9.00 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	9 in
Height	9 in
Length	40.88 in
Length - Ground Shield	15.50 in
Length - Insulation Above Flange	9.80 in
Length - Insulation Below Flange	4.78 in
Length - Live Part Bottom	4.10 in
Length - Live Part Top	3.20 in
Length - Minimum Oil Immersion Level	15.50 in
Sealing Surface Inside Diameter	3.01 in
Sealing Surface Outside Diameter	6.37 in
Top Terminal Min. Thread Length	2.5 in
Weight	42 lb
Width	9 in

## Electrical Ratings

BIL	150 kV
Current Rating	1200 A
Minimum Creepage	21.1 in
Minimum Strike	10.8 in
Withstand Voltage - 60 Hz Dry	60 kV
kV Class	25 kV

## Certifications And Compliance

Industry Standard(s) IEEE C57.19.01

## Product Assets

[Installation Manuals - SDC™ Bushing General Handling and](#)

[Maintenance Guide - Electro Composites](#)

[Sales Drawings - 926-02\\_5503-9570](#)

[Video - ElectroComposites Factory Tour: St. Jerome](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
EC-150012B92602-SPEC-EN | REV 6/2024