

SDC™ Composite Bushing - 25kV

By Electro Composites
Catalog # 150-020-T-415-00

SDC™ 25kV-2000 A Transformer Condenser Bushing, Solid-Dielectric-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21" Min. Oil Immersion Level/CT Pocket Length, 30.6" Min. Creepage Length

Features

- SDC™ - Solid Dielectric Capacitance Graded Composite Construction
- EC-APG-02 Cycloaliphatic Epoxy Compound for Optimal Performance
- No oil, paper or porcelain
- Can be mounted vertically or horizontally
- Meets IEEE C57.19.01 Electrical and Mechanical Requirements

Application

Transformer

General

Bottom Terminal Type	2-12
Catalog Number	150-020-T-415-00
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	APG-02 - Cycloaliphatic Epoxy
Mounting Position	Vertical to Horizontal
Number of Flange Mounting Holes	4
Plating - Bottom Terminal	None
Test Tap	Yes
Top Terminal Plating	None
Top Terminal Type	2-12
Type	SDC - Solid Dielectric Capacitor

Dimensions

Above Flange Length	18 in
Below Flange Length	29.5 in
Diameter - Above Flange Maximum	8.64 in
Diameter - Below Flange Maximum D <gt; 1"	4.15 in
Diameter - Below Flange Maximum P	4.34 in
Diameter - Conductor Outside Under Insulation	2 in
Diameter - Live Part Bottom	2.00 in



*Representative Image

Diameter - Live Part Top	3.50 in
Diameter - Rod / Tube	2 in
Dimensions	47.50 in x 8.75 in x 8.75 in
Effective Length - Bottom Terminal	2.13 in
Effective Length - Top Terminal	2.13 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.75 in
Height	8.75 in
Length	47.5 in
Length - Ground Shield	21.00 in
Length - Insulated Section	40.5 in
Length - Insulation Above Flange	11.20 in
Length - Insulation Below Flange	5.00 in
Length - Live Part Bottom	3.50 in
Length - Live Part Top	3.50 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Inside Diameter	4.37 in
Sealing Surface Outside Diameter	6.37 in
Thickness	1.075 in
Top Terminal Min. Thread Length	2.13 in
Weight	88 lb
Width	8.75 in

Electrical Ratings

BIL	150 kV
Current Rating	2000 A
Minimum Creepage	30.6 in
Minimum Strike	13.4 in
Withstand Voltage - 60 Hz Dry kV Class	60 kV
	25 kV

Certifications And Compliance

Industry Standard(s)	IEEE C57.19.01
----------------------	----------------

Product Assets

Catalogs - Electro Composites SDC™ composite bushings
Installation Manuals - SDC™ Bushing General Handling and
Maintenance Guide - Electro Composites
Literature - SDC™ HV Generator Bushings - Electro Composites
Literature - How an SDC Bushing Test Tap is Constructed
Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES DE TYPE
GSU
Literature - SDC™ GSU Bushings - Electro Composites

Literature - TRAVERSÉE SDC™ ÉLECTRO COMPOSITES POUR
GÉNÉRATEUR
Literature - Apparatus Bushings Selection Guide
Literature - ÉLECTRO COMPOSITES TRAVERSÉE HAUTE
TENSION SDC™
Literature - SDC™ HV Bushings - Electro Composites
Sales Drawings - 415-00_5023-4906
Specifications - 150020T41500
Video - ElectroComposites Factory Tour: St. Jerome



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
EC-150020T41500-SPEC-EN | REV 3/2025